

# PAL-LOOP



Cat.No.3842



**Special Anniversary model! New Continuous Measurement Feature expands traditional measuring methods.**

## Easy Continuous Measurements!

Once the START key is pressed, measurements are taken every second.

## Conventional Single Measurement Option!

2 options tailored to meet your needs - select either the new continuous or conventional single measurement mode.

## Measurement Method



Apply 2-3 drops onto the prism surface.



Press the START key.



The Brix (%) will be displayed in 3 seconds. The PAL-LOOP will take continuous measurements, displaying the measured Brix value each second.



## Features

- 2 Measurement modes
- Calibration with water only
- Measurement in 3 seconds
- Extremely water resistant (IP65)
- Light & compact, 100g
- Ergonomically designed for easy, one-handed operation
- Convenient storage case
- Automatic Temp. Compensation (ATC)
- Designed with a strap holder option



Can be washed under running water

Actual Size

## Specifications

Measurement mode	: ① Regular (single measurement) ② Continuous (measure and display repeatedly)
Measurement range	: Brix 0.0 to 85.0%
Resolution	: Brix 0.1%
Measurement accuracy	: Brix ±0.2%
Repeatability	: Brix ±0.1%
Ambient Temperature	: 10 to 40°C
Measurement Temperature	: 10 to 75°C (Automatic Temperature Compensation)
Sample volume	: 0.3ml or more
Measurement time	: 3 seconds
Power supply	: AAA alkaline battery × 2
Battery life	: Approx. 11,000 measurements (Using new alkaline batteries)
International Protection Class	: IP65 Water resistant
Dimensions and weight	: 55(W)×31(D)×09(H)mm, 100g

All ATAGO refractometers are designed and manufactured in Japan.

**HACCP GMP GLP**

ATAGO products comply with HACCP, GMP, and GLP system standards.

## ATAGO CO., LTD.

Headquarters: The Front Tower Shiba Koen, 23rd Floor  
2-6-3 Shiba-koen, Minato-ku, Tokyo 105-0011, Japan  
TEL : 81-3-3431-1943 FAX : 81-3-3431-1945  
overseas@atago.net http://www.atago.net/

### ATAGO U.S.A., Inc.

TEL : 1-425-637-2107 customerservice@atago-usa.com

### ATAGO INDIA Instruments Pvt. Ltd.

TEL : 91-22-2833-8038 / 8076 customerservice@atago-india.com

### ATAGO (THAILAND) Co., Ltd.

TEL : 662-982-8718-9 customerservice@atago-thailand.com

### ATAGO BRASIL Ltda.

TEL : 55 16 3916-6000 customerservice@atago-brasil.com

### ATAGO ITALIA s.r.l.

TEL : 39 2 36557267 customerservice@atago-italia.com

### ATAGO CHINA Guangzhou Co., Ltd.

TEL : 86 20-38106065 info@atago-china.com



\* Specifications and appearance are subject to change without notice.